

Hexagon head bolt DIN 931 Steel Plain 12.9 M10X40

Article number	04108.100.040
Brand	-
UBB	955351408260
UNSPSC	31161620
EAN	8715493849624
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	40 mm
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

DIN	931
NF	E25-112
ISO	4014
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	40
P	1.5
s	17

Technical Drawing

