

Hexagon head bolt DIN 931 Steel Plain 12.9 M10X50



Article number	04108.100.050
Brand	-
UBB	955351408344
UNSPSC	31161620
EAN	8715493849631
PKG. of 100	Full Box Only

Technical Parameters

Diameter (d-D)	M10
Length (L) (mm)	50
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Wrench width (s) (mm)	17
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	931
NF	E25-112
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm<L≤200mm	32
b (min.): L>200mm	45
b (min.): L≤125mm	26
k	6.4
P	1.50
s	17

Technical Drawing

