

Hexagon head bolt DIN 931 Steel Plain 12.9 M12X70

Article number	04108.120.070
Brand	-
UBB	955351409250
UNSPSC	31161620
EAN	8715493849723
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	70 mm
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

ASME	B18.2.3.1M
DIN	931
NF	E25-112
NEN	1555
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	70
P	1.75
s	19

Technical Drawing

