

Hexagon head bolt DIN 931 Steel Plain 12.9 M16X60

Article number	04108.160.060
Brand	-
UBB	955351410555
UNSPSC	31161620
EAN	8715493849853
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Length	60 mm
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NF	E25-112
DIN	931
ISO	4014
NEN	1555
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
k	10
L (mm)	60
P	2
s	24

Technical Drawing

