

Hexagon head bolt DIN 931 Steel Plain 12.9 M16X80



Article No.	04108.160.080
Brand	-
UBB	955351410712
UNSPSC	31161620
EAN	8715493849877
PKG. of 25	Full Box Only

Technical Parameters

Diameter (d-D)	M16
Length (L) (mm)	80
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

ASME	B18.2.3.1M
NF	E25-112
DIN	931
ISO	4014

Technical Specification

b (min.): 125mm<L≤200mm	44
b (min.): L>200mm	57
b (min.): L≤125mm	38
k	10
P	2
s	24

Technical Drawing

