

Hexagon head bolt DIN 931 Steel Plain 12.9 M20X160

Article number	04108.200.160
Brand	-
UBB	955351164046
UNSPSC	31161620
EAN	8715493356214
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M20
Length	160 mm
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ISO	4014
ASME	B18.2.3.1M
NF	E25-112
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	160
P	2.5
s	30

Technical Drawing

