

Hexagon head bolt DIN 931 Steel Plain 12.9 M30X90



Article number	04108.300.090
Brand	-
UBB	955351412536
UNSPSC	31161620
EAN	8715493850057
PKG. of 10	Full Box Only

Technical Parameters

Diameter (d-D)	M30
Length (L) (mm)	90
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	931
ASME	B18.2.3.1M
ISO	4014
NF	E25-112

Technical Specification

b (min.): 125mm<L≤200mm	72
b (min.): L>200mm	85
b (min.): L≤125mm	66
k	18.7
P	3.50
s	46

Technical Drawing

