

## Hexagon head bolt DIN 931 Steel Plain 12.9 M30X120

|                |               |
|----------------|---------------|
| Article number | 04108.300.120 |
| Brand          | -             |
| UBB            | 955351412874  |
| UNSPSC         | 31161620      |
| EAN            | 8715493850088 |
| PKG. of 10     | Full Box Only |

### Technical Parameters

|                   |               |
|-------------------|---------------|
| Diameter          | M30           |
| Length            | 120 mm        |
| Class             | 12.9          |
| Driving features  | Hexagon       |
| Head shape        | Hexagon head  |
| Material          | Steel         |
| Thread direction  | Right         |
| Surface treatment | Plain         |
| Thread            | Metric thread |

Info      Warning:  
electroplating of  
these products may  
cause hydrogen  
embrittlement.

### Standards

|      |            |
|------|------------|
| ASME | B18.2.3.1M |
| ISO  | 4014       |
| NEN  | 1555       |
| DIN  | 931        |
| NF   | E25-112    |

### Technical Specification

|                           |      |
|---------------------------|------|
| b (min.):<br>125mmL≤200mm | 72   |
| b (min.): L200mm          | 85   |
| b (min.): L≤125mm         | 66   |
| d-D                       | M30  |
| k                         | 18.7 |
| L (mm)                    | 120  |
| P                         | 3.5  |
| s                         | 46   |

### Technical Drawing

