



Hexagon head screw DIN 933 Steel Plain 10.9 M10X25

Article No.	04110.100.025
Brand	-
UBB	950351330812
UNSPSC	31161620
EAN	8715492117465
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M10
Length (L) (mm)	25
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Wrench width (s) (mm)	17
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

ASME	B18.2.3.1M
DIN	933
ISO	4017
NF	E25-114

Technical Specification

k	6.4
P	1.50
s	17

Technical Drawing

