

Hexagon head screw DIN 933 Steel Plain 10.9 DIN 933 M10X55



Article No.	04110.100.055
Brand	-
UBB	954351349038
UNSPSC	31161620
EAN	8715492117526
PKG. of 100	Full Box Only

Technical Parameters

Diameter (d-D)	M10
Length (L) (mm)	55
Class	10.9
Driving features	Hexagon
Extra info	DIN 933
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Wrench width	17

Info
 Warning:
 electroplating of
 these products may
 cause hydrogen
 embrittlement.

Standards

NEN	1568
DIN	933
NF	E25-114
ASME	B18.2.3.1M
ISO	4017

Technical Specification

P	1.50
k	6.4
s	17

Technical Drawing

