



Hexagon head screw DIN 933 Steel Plain 10.9 M10X60

| | |
|----------------|---------------|
| Article number | 04110.100.060 |
| Brand | - |
| UBB | 952351205408 |
| UNSPSC | 31161620 |
| EAN | 8715492117533 |
| PKG. of 100 | Full Box Only |

Technical Parameters

| | |
|-----------------------|---|
| Diameter (d-D) | M10 |
| Length (L) (mm) | 60 |
| Class | 10.9 |
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Plain |
| Thread | Metric thread |
| Wrench width (s) (mm) | 17 |
| Info | Warning: electroplating of these products may cause hydrogen embrittlement. |

Standards

| | |
|------|------------|
| ASME | B18.2.3.1M |
| NF | E25-114 |
| ISO | 4017 |
| DIN | 933 |

Technical Specification

| | |
|---|------|
| k | 6.4 |
| P | 1.50 |
| s | 17 |

Technical Drawing

