

Hexagon head screw ISO 4017 Steel Dacromet 500 LC Grade A 10.9 M6X12

Article number	04113.060.012
Brand	-
UBB	952351670619
UNSPSC	31161620
EAN	8715492118585
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	12 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Dacromet 500 LC Grade A
Thread	Metric thread

Standards

NEN	1568
ISO	4017
NF	E25-114
ASME	B18.2.3.1M
DIN	933

Technical Specification

d-D	M6
k	4
L (mm)	12
P	1
s	10

Technical Drawing

