

Hexagon head screw ISO 4017 Steel Dacromet 500 LC Grade A 10.9 M16X40

Article number	04113.160.040
Brand	-
UBB	952351672516
UNSPSC	31161620
EAN	8715492118868
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Length	40 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Dacromet 500 LC Grade A
Thread	Metric thread

Standards

NF	E25-114
ASME	B18.2.3.1M
DIN	933
NEN	1568
ISO	4017

Technical Specification

d-D	M16
k	10
L (mm)	40
P	2
s	24

Technical Drawing

