



## Hexagon head screw ISO 4017 Steel Dacromet 500 LC Grade A 10.9 M16X60

Article No.	04113.160.060
Brand	-
UBB	954351248131
UNSPSC	31161620
EAN	8715492118899
PKG. of 25	Full Box Only

### Technical Parameters

Diameter (d-D)	M16
Length (L) (mm)	60
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Dacromet 500 LC Grade A
Thread	Metric thread

**Info**  
 A DACROMET® surface coating eliminates the possibilities of damage which can arise due to hydrogen embrittlement.

### Standards

NF	E25-114
ASME	B18.2.3.1M
DIN	933
ISO	4017

### Technical Specification

k	10
P	2
s	24

### Technical Drawing

