

## Hexagon head screw DIN 933 Steel Plain 12.9 M10X30

|                |               |
|----------------|---------------|
| Article number | 04118.100.030 |
| Brand          | -             |
| UBB            | 953351785704  |
| UNSPSC         | 31161620      |
| EAN            | 8715492119087 |
| PKG. of 200    | Full Box Only |

### Technical Parameters

|                   |               |
|-------------------|---------------|
| Diameter          | M10           |
| Length            | 30 mm         |
| Class             | 12.9          |
| Driving features  | Hexagon       |
| Head shape        | Hexagon head  |
| Material          | Steel         |
| Thread direction  | Right         |
| Surface treatment | Plain         |
| Thread            | Metric thread |

Info  
Warning:  
electroplating of  
these products may  
cause hydrogen  
embrittlement.

### Standards

|      |            |
|------|------------|
| ISO  | 4017       |
| NEN  | 1568       |
| ASME | B18.2.3.1M |
| NF   | E25-114    |
| DIN  | 933        |

### Technical Specification

|        |     |
|--------|-----|
| d-D    | M10 |
| k      | 6.4 |
| L (mm) | 30  |
| P      | 1.5 |
| s      | 17  |

### Technical Drawing

