



Hexagon head screw DIN 933 Steel Plain 12.9 M12X25

Article number 04118.120.025

Brand -

UBB 953351786041

UNSPSC 31161620

EAN 8715492119131

PKG. of 100 Full Box Only

Technical Parameters

Diameter (d-D)	M12
Length (L) (mm)	25
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Wrench width (s) (mm)	19

Standards

DIN	933
ISO	4017
NF	E25-114
ASME	B18.2.3.1M

Info	Warning: electroplating of these products may cause hydrogen embrittlement.
------	---

Technical Specification

k	7.5
P	1.75
s	19

Technical Drawing

