

Hexagon nut DIN 934 Steel
Zinc plated |10| M3

Article number	04121.030.001
Brand	-
UBB	950355814381
UNSPSC	31161727
EAN	8715492119667
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M3
Class	10
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-401
NEN	1560
DIN	934

Technical Specification

d-D	M3
m	2.4
P	0.5
s	5.5

Technical Drawing

