

Hexagon nut DIN 934 Steel Zinc plated yellow passivated |10| M12

Article number	04122.120.001
Brand	-
UBB	950355895711
UNSPSC	31161727
EAN	8715493851047
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Class	10
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NF	E25-401
NEN	1560
DIN	934

Technical Specification

d-D	M12
m	10
P	1.75
s	19

Technical Drawing

