

Hexagon nut ISO-Metric
thread ISO 4032 Steel Hot
dip galvanized 10 ISO metric
M36

Article number	04128.360.001
Brand	-
UBB	500648941861
UNSPSC	31161727
EAN	8717077238312
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M36
Class	10
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

ISO metric hot dip galvanized nuts are manufactured with thread tolerance class 6H and mate with externally threaded parts (bolts, threaded rods) that are manufactured with thread tolerance class 6az before coating.As the nut thread is tapped after galvanizing the threads are not coated. The corrosion resistance however is not influenced disadvantageously

Standards

ISO	4032
-----	------

as the thread will be
protected by the zinc
layer of the mating
part.ISO metric

Technical Specification

d-D	M36
m (max.)	31
P	4
s	55

Technical Drawing

