



Hexagon flange bolt MF DIN 6921 Steel Plain 10.9 M10X1,25X60

Article number	04135.100.060
Brand	-
UBB	955351423764
UNSPSC	31161620
EAN	8715493858121
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	60 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric fine thread

Info

Warning:
electroplating of
these products may
cause hydrogen
embrittlement. Special
features of hexagon
bolts with flange: The
flange enables built
up forces to be
spread over a larger
area, consequently
resulting in
lower surface
pressure. Large holes
(oversized) and/or
tooling holes can
be covered by the
flange. A washer is
not necessary.

Standards

EN	≈1665
ISO	≈4162
DIN	6921
ASME	≈B18.2.3.4M

Technical Specification

b (min.)	26
d-D	M10
dc (max.)	22.3
k (max.)	9.2
L (mm)	60
P	1.25
s	15

Technical Drawing

