



Hexagon flange bolt MF DIN 6921 Steel Plain 10.9 M12X1,50X40

Article number	04135.120.040
Brand	-
UBB	955351424184
UNSPSC	31161620
EAN	8715493858169
PKG. of 100	Full Box Only

Technical Parameters

Diameter (d-D)	M12
Length (L) (mm)	40
P	1.50
Info	Special features of hexagon bolts with flange: The flange enables built up forces to be spread over a larger area, consequently resulting in lower surface pressure. Large holes (oversized) and/or tooling holes can be covered by the flange. A washer is not necessary.
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric fine thread
Info	Warning: electroplating of these products may

Standards

EN	≈1665
DIN	6921
ISO	≈4162
ASME	≈B18.2.3.4M

cause hydrogen embrittlement.

FABORY
OF COURSE.

Technical Specification

b (min.)	30
d_c (max.)	26.6
k (max.)	11.5
s	16

Technical Drawing

