



## Hexagon flange bolt MF DIN 6921 Steel Plain 10.9 M14X1,50X40

Article number	04135.140.040
Brand	-
UBB	955351424598
UNSPSC	31161620
EAN	8715493858206
PKG. of 50	Full Box Only

### Technical Parameters

Diameter	M14
Length	40 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric fine thread

#### Info

Warning:  
electroplating of these products may cause hydrogen embrittlement. Special features of hexagon bolts with flange: The flange enables built up forces to be spread over a larger area, consequently resulting in lower surface pressure. Large holes (oversized) and/or tooling holes can be covered by the flange. A washer is not necessary.

### Standards

DIN	6921
EN	≈1665
ASME	≈B18.2.3.4M
ISO	≈4162

Technical Specification

b (min.)	34
d-D	M14
dc (max.)	30.5
k (max.)	12.8
L (mm)	40
P	1.5
s	18

Technical Drawing

