



**Hexagon flange bolt DIN  
6921 Steel Zinc plated 10.9  
M5X10**

Article number	04137.050.010
Brand	-
UBB	500648942935
UNSPSC	31161620
EAN	8717077238428
PKG. of 500	Full Box Only

**Technical Parameters**

Diameter	M5
Length	10 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info      Warning:  
electroplating of  
these products may  
cause hydrogen  
embrittlement. Specific  
features of hexagon  
bolts with flange: The  
flange enables built  
up forces under  
the bolt head to be  
spread over a larger  
area, consequently  
resulting in  
lower surface  
pressure. Large  
(oversized) holes  
and/or tooling holes  
can be covered by  
the flange. Washers  
are not necessary.

**Standards**

EN	≈1665
DIN	6921
ISO	≈4162
ASME	≈B18.2.3.4M

Technical Specification

b (min.)	16
d-D	M5
dc (max.)	11.8
k (max.)	5.4
L (mm)	10
P	0.8
s	8

Technical Drawing

