



Hexagon flange bolt DIN 6921 Steel Zinc plated 10.9 M8X10

Article number	04137.080.010
Brand	-
UBB	500648943842
UNSPSC	31161620
EAN	8717077238510
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M8
Length (L) (mm)	10
Info	Specific features of hexagon bolts with flange: The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure. Large (oversized) holes and/or tooling holes can be covered by the flange. Washers are not necessary.
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may

Standards

DIN	6921
ASME	≈B18.2.3.4M
EN	≈1665
ISO	≈4162

cause hydrogen embrittlement.

FABUKY OF COURSE.

Technical Specification

b (min.)	22
d_c (max.)	18
k (max.)	8.1
P	1.25
s	13

Technical Drawing

