



## Hexagon flange bolt DIN 6921 Steel Zinc plated 10.9 M8X20

Article number	04137.080.020
Brand	-
UBB	500648944006
UNSPSC	31161620
EAN	8717077238534
PKG. of 200	Full Box Only

### Technical Parameters

Diameter (d-D)	M8
Length (L) (mm)	20
Info	Specific features of hexagon bolts with flange: The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure. Large (oversized) holes and/or tooling holes can be covered by the flange. Washers are not necessary.
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may

### Standards

EN	≈1665
ISO	≈4162
ASME	≈B18.2.3.4M
DIN	6921

cause hydrogen embrittlement.

**FABUKY** OF COURSE.

## Technical Specification

b (min.)	22
$d_c$ (max.)	18
k (max.)	8.1
P	1.25
s	13

## Technical Drawing

