



**Hexagon flange bolt DIN
6921 Steel Zinc plated 10.9
M8X20**

Article number	04137.080.020
Brand	-
UBB	500648944006
UNSPSC	31161620
EAN	8717077238534
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	20 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info

Warning:
electroplating of
these products may
cause hydrogen
embrittlement. Specific
features of hexagon
bolts with flange: The
flange enables built
up forces under
the bolt head to be
spread over a larger
area, consequently
resulting in
lower surface
pressure. Large
(oversized) holes
and/or tooling holes
can be covered by
the flange. Washers
are not necessary.

Standards

EN	≈1665
ISO	≈4162
ASME	≈B18.2.3.4M
DIN	6921

Technical Specification

b (min.)	22
d-D	M8
dc (max.)	18
k (max.)	8.1
L (mm)	20
P	1.25
s	13

Technical Drawing

