



Hexagon flange bolt DIN 6921 Steel Zinc plated 10.9 M8X30

Article number	04137.080.030
Brand	-
UBB	500648944188
UNSPSC	31161620
EAN	8717077238541
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	30 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info

Warning: electroplating of these products may cause hydrogen embrittlement. Specific features of hexagon bolts with flange: The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure. Large (oversized) holes and/or tooling holes can be covered by the flange. Washers are not necessary.

Standards

DIN	6921
ISO	≈4162
EN	≈1665
ASME	≈B18.2.3.4M

Technical Specification

b (min.)	22
d-D	M8
dc (max.)	18
k (max.)	8.1
L (mm)	30
P	1.25
s	13

Technical Drawing

