



**Hexagon flange bolt DIN  
6921 Steel Zinc plated 10.9  
M10X30**

Article number	04137.100.030
Brand	-
UBB	500648944758
UNSPSC	31161620
EAN	8717077238602
PKG. of 200	Full Box Only

**Technical Parameters**

Diameter	M10
Length	30 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info      Warning:  
electroplating of  
these products may  
cause hydrogen  
embrittlement. Specific  
features of hexagon  
bolts with flange: The  
flange enables built  
up forces under  
the bolt head to be  
spread over a larger  
area, consequently  
resulting in  
lower surface  
pressure. Large  
(oversized) holes  
and/or tooling holes  
can be covered by  
the flange. Washers  
are not necessary.

**Standards**

ISO	≈4162
ASME	≈B18.2.3.4M
EN	≈1665
DIN	6921

Technical Specification

b (min.)	26
d-D	M10
dc (max.)	22.3
k (max.)	9.2
L (mm)	30
P	1.5
s	15

Technical Drawing

