



Hexagon flange bolt DIN  
6921 Steel Zinc plated 10.9  
M12X25

Article number	04137.120.025
Brand	-
UBB	500648945177
UNSPSC	31161620
EAN	8717077238640
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	25 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info

Warning:  
electroplating of  
these products may  
cause hydrogen  
embrittlement. Specific  
features of hexagon  
bolts with flange: The  
flange enables built  
up forces under  
the bolt head to be  
spread over a larger  
area, consequently  
resulting in  
lower surface  
pressure. Large  
(oversized) holes  
and/or tooling holes  
can be covered by  
the flange. Washers  
are not necessary.

Standards

ASME	≈B18.2.3.4M
ISO	≈4162
EN	≈1665
DIN	6921

Technical Specification

b (min.)	30
d-D	M12
dc (max.)	26.6
k (max.)	11.5
L (mm)	25
P	1.75
s	16

Technical Drawing

