



Hexagon flange bolt DIN 6921 Steel Zinc plated 10.9 M12X40

Article number 04137.120.040

Brand -

UBB 500648945417

UNSPSC 31161620

EAN 8717077238671

PKG. of 100 Full Box Only

Technical Parameters

Diameter (d-D) M12

Length (L) (mm) 40

Info
Specific features of hexagon bolts with flange: The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure. Large (oversized) holes and/or tooling holes can be covered by the flange. Washers are not necessary.

Class 10.9

Driving features Hexagon

Head shape Hexagon head

Material Steel

Thread direction Right

Surface treatment Zinc plated

Thread Metric thread

Info
Warning: electroplating of these products may

Standards

DIN 6921

ASME ≈B18.2.3.4M

ISO ≈4162

EN ≈1665

cause hydrogen embrittlement.

FABUKY OF COURSE.

Technical Specification

b (min.)	30
d_c (max.)	26.6
k (max.)	11.5
P	1.75
s	16

Technical Drawing

