



Hexagon flange bolt EN 1665 Steel Zinc plated 10.9 M5X12

Article number	04140.050.012
Brand	-
UBB	500650799447
UNSPSC	31162400
EAN	8717077294394
PKG. of 500	Full Box Only

Technical Parameters

Diameter (d-D)	M5
Length (L) (mm)	12
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

ISO	≈4162
EN	1665
ASME	≈B18.2.3.4M
DIN	≈6921

Technical Specification

b (min.)	16
d _c (max.)	11.8
k (max.)	5.8
P	0.80
s	8

Technical Drawing

