



Hexagon flange bolt EN 1665 Steel Zinc plated 10.9 M6X16

Article number	04140.060.016
Brand	-
UBB	500650799850
UNSPSC	31162400
EAN	8717077294431
PKG. of 500	Full Box Only

Technical Parameters

Diameter (d-D)	M6
Length (L) (mm)	16
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	≈6921
ASME	≈B18.2.3.4M
ISO	≈4162
EN	1665

Technical Specification

b (min.)	18
d _c (max.)	14.2
k (max.)	6.6
P	1
s	10

Technical Drawing

