

Hexagon head bolt MF DIN 960 Steel Plain 10.9 M8X1,00X80



Article number	04160.080.080
Brand	-
UBB	953351780184
UNSPSC	31161620
EAN	8715492120595
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	80 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric fine thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NF	E25-152
DIN	960
ISO	8765
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L200mm	41
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	80
P	1
s	13

Technical Drawing

