



Hexagon head bolt MEF DIN 960 Steel Plain 10.9 M10X1,00X45

Article number	04161.100.045
Brand	-
UBB	500645030502
UNSPSC	31161620
EAN	8717077052697
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	45 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric extra fine thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

DIN	960
NEN	1555
ISO	8765
NF	E25-152

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	45
P	1

Technical Drawing



