

Hexagon head bolt MEF DIN 960 Steel Plain 10.9 M10X1,00X60



Article number	04161.100.060
Brand	-
UBB	950351335290
UNSPSC	31161620
EAN	8715492121165
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	60 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric extra fine thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NF	E25-152
ISO	8765
DIN	960
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	60
P	1

Technical Drawing



