



Hexagon head bolt MEF DIN 960 Steel Plain 10.9 M10X1,00X90

Article number	04161.100.090
Brand	-
UBB	950351335522
UNSPSC	31161620
EAN	8715492121196
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	90 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric extra fine thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NEN	1555
ISO	8765
DIN	960
NF	E25-152

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	90
P	1

Technical Drawing



