



Hexagon head bolt MEF DIN 960 Steel Plain 10.9 M18X1,50X65

Article number	04161.180.065
Brand	-
UBB	500644711912
UNSPSC	31161620
EAN	8717077019744
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M18
Length	65 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric extra fine thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ISO	8765
DIN	960
NF	E25-152
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	48
b (min.): L200mm	61
b (min.): L≤125mm	42
d-D	M18
k	11.5
L (mm)	65
P	1.5

Technical Drawing



