

Hexagon head bolt MEF DIN 960 Steel Plain 10.9 M22X1,50X140



Article number	04161.220.140
Brand	-
UBB	500644713322
UNSPSC	31161620
EAN	8717077019881
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M22
Length	140 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric extra fine thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NEN	1555
ISO	8765
NF	E25-152
DIN	960

Technical Specification

b (min.): 125mmL≤200mm	56
b (min.): L200mm	69
b (min.): L≤125mm	50
d-D	M22
k	14
L (mm)	140
P	1.5

Technical Drawing



