



Hexagon head bolt MF DIN 960 Steel Zinc plated 10.9 M14X1,50X60

Article number	04162.140.060
Brand	-
UBB	500648165446
UNSPSC	31161620
EAN	8717077212411
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	60 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric fine thread

Info

Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NF	E25-152
ISO	8765
NEN	1555
DIN	960

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	60
P	1.5
s	22

Technical Drawing

