

Hexagon nut DIN 934 Steel
Plain |12| M10

Article number	04190.100.001
Brand	-
UBB	950355326964
UNSPSC	31161727
EAN	8715492123138
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M10
Class	12
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	934
NEN	1560
NF	E25-401

Technical Specification

d-D	M10
m	8
P	1.5
s	17

Technical Drawing

