



Hexagon socket head cap screw DIN 912 Steel Plain 10.9 M3X20

Article number	07015.030.020
Brand	-
UBB	500645040667
UNSPSC	31161605
EAN	8717077053700
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	20 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

BS	4168-1
NEN	1241
NF	E25-125
ISO	4762
ASME	B18.3.1M
DIN	912

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if $L \leq$	20
k (max.)	3
L (mm)	20
P	0.5
s	2.5

Technical Drawing

