



Hexagon socket head cap screw DIN 912 Steel Plain 10.9 M18X45

Article number	07015.180.045
Brand	-
UBB	500645057828
UNSPSC	31161605
EAN	8717077045996
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M18
Length	45 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

BS	4168-1
NF	E25-125
ISO	4762
DIN	912
ASME	B18.3.1M
NEN	1241

Technical Specification

b	48
d-D	M18
dk (max.)	27
Full thread if $L \leq$	65
k (max.)	18
L (mm)	45
P	2.5
s	14

Technical Drawing

