



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M3X16

Article number	07023.030.016
Brand	-
UBB	500647934537
UNSPSC	31161605
EAN	8717077281479
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	16 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ISO	4762
BS	4168-1
NF	E25-125
ASME	B18.3.1M
NEN	1241
DIN	912

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if $L \leq$	20
k (max.)	3
L (mm)	16
P	0.5
s	2.5

Technical Drawing

