



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M3X20

Article number	07023.030.020
Brand	-
UBB	500647934610
UNSPSC	31161605
EAN	8717077281486
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	20 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

DIN	912
NF	E25-125
ASME	B18.3.1M
BS	4168-1
NEN	1241
ISO	4762

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if $L \leq$	20
k (max.)	3
L (mm)	20
P	0.5
s	2.5

Technical Drawing

