



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M3X30

Article number	07023.030.030
Brand	-
UBB	500647934875
UNSPSC	31161605
EAN	8717077281509
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	30 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NEN	1241
DIN	912
BS	4168-1
ASME	B18.3.1M
NF	E25-125
ISO	4762

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if $L \leq$	20
k (max.)	3
L (mm)	30
P	0.5
s	2.5

Technical Drawing

