



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M6X25

Article number	07023.060.025
Brand	-
UBB	500647940302
UNSPSC	31161605
EAN	8717077282056
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M6
Length	25 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ASME	B18.3.1M
ISO	4762
BS	4168-1
NF	E25-125
NEN	1241
DIN	912

Technical Specification

b	24
d-D	M6
dk (max.)	10
Full thread if $L \leq$	30
k (max.)	6
L (mm)	25
P	1
s	5

Technical Drawing

