



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M6X50

Article number	07023.060.050
Brand	-
UBB	500647940898
UNSPSC	31161605
EAN	8717077282100
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	50 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

BS	4168-1
DIN	912
NEN	1241
ASME	B18.3.1M
ISO	4762
NF	E25-125

Technical Specification

b	24
d-D	M6
dk (max.)	10
Full thread if $L \leq$	30
k (max.)	6
L (mm)	50
P	1
s	5

Technical Drawing

