



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M10X90

Article number	07023.100.090
Brand	-
UBB	500647947091
UNSPSC	31161605
EAN	8717077282728
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	90 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ASME	B18.3.1M
NF	E25-125
ISO	4762
DIN	912
NEN	1241
BS	4168-1

Technical Specification

b	32
d-D	M10
dk (max.)	16
Full thread if $L \leq$	40
k (max.)	10
L (mm)	90
P	1.5
s	8

Technical Drawing

