



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M10X210

Article number	07023.100.210
Brand	-
UBB	500647948081
UNSPSC	31161605
EAN	8717077282827
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	210 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NEN	1241
ASME	B18.3.1M
BS	4168-1
DIN	912
ISO	4762
NF	E25-125

Technical Specification

b	32
d-D	M10
dk (max.)	16
Full thread if $L \leq$	40
k (max.)	10
L (mm)	210
P	1.5
s	8

Technical Drawing

