



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M14X90

Article number	07023.140.090
Brand	-
UBB	500647953594
UNSPSC	31161605
EAN	8717077283374
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	90 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NF	E25-125
NEN	1241
DIN	912
ASME	B18.3.1M
BS	4168-1
ISO	4762

Technical Specification

b	40
d-D	M14
dk (max.)	21
Full thread if $L \leq$	55
k (max.)	14
L (mm)	90
P	2
s	12

Technical Drawing

